


**ASTM D7169 (C9-C120) Standard on ZB-1XT SimDist 5x0.53x0.09, C10 - C120****Column:** Zebtron<sup>™</sup> ZB-1XT SimDist Metal, GC Cap. Column 5 m x 0.53 mm x 0.09 µm, Ea**Phase:** 100% Dimethylpolysiloxane**Dimensions:** 5 meters x 0.53 mm x 0.09 µm**Order No:** 7AK-G026-55**Oven Profile:** 35 °C to 430 °C @ 9 °C/min for 10 min.**Carrier Gas:** Constant Flow Helium, 34 mL/min**Injection:** On-Column :1 1 µL @ 38°C**Detection:** Refractive Index (450°C)**Analyst Note:** This chromatogram has been baseline subtracted. Sample was D2887 calibration mix with PolyWAX 1000 in**Products used in this application:**

## ASTM D7169 (C9-C120) Standard on ZB-1XT SimDist 5x0.53x0.09, C10 - C120

### ANALYTES:

- 1 Decane (C10)
- 2 Undecane (C11)
- 3 Dodecane (C12)
- 4 Tetracontane (C40)
- 5 Tetratetracontane (C44)
- 6 Pentacontane (C50)
- 7 Dopentacontane (C52)
- 8 Hectane (C100)
- 9 Decahectane (C110)
- 10 Icosahectane (C120)

